



Industrial Spec Grade Turnlok Registered 20A Non-NEMA 3-Wire Connector Back Front Body



Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info			
Product Line	Pass & Seymour	Color	Black
UPC Number	785007731316	Country Of Origin	Mexico
Features	Dust Resistant	Application Sector	Industrial
Standard	UL 498	Warranty Type	1-Year
Type	Connector		
Dimensions			
Product Width US	1.531 in	Product Depth US	2.624 in
Product Height US	1.531 in		
Technical Information			
Connector Style	Locking	Flanged	No
Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	3
Amperage	20 A	Number of Poles	3-Way
Indoor/Outdoor	Indoor	Number of Phases	3

Voltage	125/250 V
---------	-----------
