



Double pole, Single Phase AC Manual Motor Controller 30 amp, 600 watts, Suitable as Motor Disconnect

Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007267655
Country Of Origin	Mexico	Material	Thermoplastic
Features	Heavy Duty Zinc Plated Steel Strap	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	CSA Listed, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Manual Controller, Tamper-Resistant

Dimensions

Product Width US	1.825 in	Product Depth US	1.753 in
Product Height US	3.67 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Load Rating	30 A @ 600 VAC	Operating Cycles	50000
Connection Location	Back and Side	Horsepower Rating	20 HP @ 600 VAC
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Double Throw	Amperage	30 A
Number of Poles	Double Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Supply Voltage	120 V	Wire Connection Type	Screw Terminals
Voltage	600.0 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
Environmental Conditions	UL94 V2		