



Pass and Seymour
Manual Controller
Part No. 7813EX



Triple-Pole, Three Phase Switch (7803) in a NEMA 7 and 9 Enclosure for Hazardous Locations. Class I - Groups C, D Class II - Groups E, F, G. 30A, 600Vs. Slotted opening on enclosures allows for lock-out, tag-out functionality.

Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007781342
Country Of Origin	Mexico	Material	Aluminum
Features	Enclosed	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Manual Controller

Dimensions

Product Width US	3.375 in	Product Depth US	4.25 in
Product Height US	5.875 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	42707
cULus Listed	Yes	CSA File Number	42707

Technical Information

Load Rating	30 A @ 600 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Triple Throw	Amperage	30 A
Number of Poles	3-Way	Requires Neutral Wire	Yes
Indoor/Outdoor	Both	Mounting Type	On-Wall
Wire Connection Type	Screw Terminals	Voltage	600.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		