



Pass and Seymour Manual Controllers Part No. 7830



Nema 3R Enclosure Aluminum

Features & Benefits

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Aluminum
Finish	Matte	UPC Number	785007078305
Country Of Origin	Mexico	Material	Aluminum
Features	Enclosed	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty
Type	Manual Controller		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	31169	cUL Listed	Yes
-------------------	-------	------------	-----

Technical Information

Load Rating	30 A @ 600 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Triple Throw	Amperage	30 A
Number of Poles	3-Way	Requires Neutral Wire	Yes
Indoor/Outdoor	Both	Mounting Type	On-Wall
Wire Connection Type	Screw Terminals	Voltage	600.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		