



Pass and Seymour
Rotary Fan Speed Control, White
Part No. 94301WV

ROTARY FAN SPEED 3AMP HI TO LO



Features & Benefits

Full range speed control.

Utilizes standard toggle wall plates.

100 percent tested for symmetry for extended fan life.

Ground lead provided.

Ferrite bar coil choke for excellent RFI suppression.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007266207
Country Of Origin	Mexico	Material	Steel, Thermoplastic
Features	Variable Speed Fan Control	Switch Type	Rotary
Number of Switches	1	Application Sector	Multi-Dwelling Unit, Residential
Warranty Type	Limited Lifetime Warranty	Type	Fan Speed Control

Dimensions

Product Width US	3.875 in	Product Weight US	0.26 lb
Product Volume US	35.514 cu in	Product Depth US	1.56 in
Product Height US	5.875 in		

Technical Information

Preset	Yes	Load Rating	120V 3A (FAN MOTOR)
Dimming Compatibility	Fan Speed Only	Frequency Rating	60 Hz
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120 VAC	Load Type	AC Fan Motor