



Pass and Seymour
Strain Relief Deluxe Cord Grips, 1/2-in NPT, 90-Degree Male
Part No. CG40690

Cord Grip Male 90-Degree, 1/2-inch NPT, 0.250-inch-0.375-inch



Features & Benefits

Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance.

They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain.

They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets.

Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007997927
Country Of Origin	India	Material	Aluminum
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)	Type	Cord Grip

Dimensions

Cable Diameter Range	0.250-0.375 in
----------------------	----------------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	69556
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	0.31 in	Grip Angle	90°
Grip Fitting	Male	Minimum Cable Range	0.375 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
NPT Thread Size	1/2 in	Mounting	Consult the Factory for Mounting Recommendations
