



Pass and Seymour
15A, 125V Extra-Hard Use Spec-Grade Corrosion-Resistant Plug, Yellow and White
Part No. CR5266X

Straight Blade Plug 2-Pole 3-Wire 15A 125V Corrosion Resistant



Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance.

Rugged two-piece cord grip provides more uniform cord retention.

Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007526783	Country Of Origin	Mexico
Features	Corrosion Resistant	Application Sector	Commercial
Standard	UL 498	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	1.516 in	Product Length US	1.752 in
------------------	----------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connector Style	Locking	Flanged	No
Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15P
Voltage	125.0 V		