



Pass and Seymour
1000 Series Cable Reel with Tri-Tap, 15 Amp, 12 AWG, 25 ft
Part No. CRCD123N25T15



1000 Series Cable Reel with Tamper-Resistant-Tap, 15A, 12 AWG, 25 ft

Features & Benefits

Made in USA	Black molded nylon construction with reinforced steel frame
Rated for indoor use	cULus Listed

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	PSCRCD123N25T15
Color	Black	UPC Number	785007198454
Country Of Origin	United States	Features	Removable Base, Retractable
Application Sector	Commercial, Data Center, Education, Industrial	Warranty Type	2-Year
Type	Cable Reel		

Technical Information

Wire Gauge	12 AWG	Cord Length	25 ft
Amperage	15 A	Number of Conductors	3
Indoor/Outdoor	Indoor	Mobile End	Triple Tap
Voltage	125.0 V		