

Commercial 1-Pole Switch, Side-Wire, 20A 120/277V.



## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                                          |                    |                        |
|--------------------|------------------------------------------|--------------------|------------------------|
| Product Line       | Pass & Seymour                           | Color              | White                  |
| Finish             | Matte                                    | UPC Number         | 785007126471           |
| Country Of Origin  | Mexico                                   | Material           | Thermoplastic          |
| Features           | Single Piece Plated Steel Mounting Strap | Switch Type        | Toggle                 |
| Number of Switches | 1                                        | Application Sector | Commercial, Industrial |

|                                       |                                |                        |                                                                |
|---------------------------------------|--------------------------------|------------------------|----------------------------------------------------------------|
| Wall Plate Included                   | No                             | Standard               | UL 498/20, FEDSPEC                                             |
| Warranty Type                         | 1-Year Limited Warranty        | Type                   | Switch                                                         |
| Dimensions                            |                                |                        |                                                                |
| Product Width US                      | 1.32 in                        | Product Depth US       | 1.073 in                                                       |
| Product Height US                     | 3.281 in                       |                        |                                                                |
| Listing Agencies / 3rd Party Agencies |                                |                        |                                                                |
| cULus ListingNumber                   | 140597                         | cULus Listed           | Yes                                                            |
| Technical Information                 |                                |                        |                                                                |
| Load Rating                           | 20 A @ 120/277 VAC             | Connection Location    | Back and Side                                                  |
| Horsepower Rating                     | 1 HP @ 120 VAC, 2 HP @ 240 VAC | Terminal Accommodation | #14 AWG - #10 AWG                                              |
| Number of Gangs                       | 1                              | Throw Type             | Single Throw                                                   |
| Amperage                              | 20 A                           | Number of Poles        | Single Pole                                                    |
| Requires Neutral Wire                 | No                             | Indoor/Outdoor         | Indoor                                                         |
| Mounting Type                         | Wall Box                       | Wire Connection Type   | Screw Terminals                                                |
| Voltage                               | 120 VAC, 277 VAC               | Load Type              | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |