



Pass and Seymour
Decorator Rotary DR Series Fan Speed Control, White
Part No. DRSC53PWV



Continuously Variable Preset Fan Speed Control

Features & Benefits

Slim design leaves more room in the box and makes installation faster and easier.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007705744
Country Of Origin	China	Material	Steel, Thermoplastic
Features	Lighted, Variable Speed Fan Control	Switch Type	Rocker, Rotary
Number of Switches	1	Application Sector	Multi-Dwelling Unit, Residential
Standard	UL Listed	Warranty Type	Limited Lifetime Warranty
Type	Fan Speed Control		

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.185 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes		
Technical Information			
Preset	Yes	Load Rating	120V 5A (Fan Control)
Operating Cycles	100000	Dimming Compatibility	Fan Speed Only
Frequency Rating	60 Hz	Number of Poles	3-Way, Single Pole
Wire Size	#14 - #12 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	AC Fan Motor		