



Pass and Seymour
Tamper-Resistant Floor Box Assembly - One Gang for Wood Sub-Floors, Nickel
Part No. FB1TRDRN



Tamper-Resistant Floor Box Assembly, #8 duplex opening. Two threaded screw plugs, Includes 3232 15A, 125A tamper-resistant receptacle. Brass.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.	Rugged diecast cover plates.
Meets UL514(c) and NEC 314.27(c).	Scrub water compliant.
With durable nickel or brass cover plates.	Dual-voltage models available.
Swing brackets mounting option eliminates drilling tile flooring for mounting screws.	Wood sub-floors only.
Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.	

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
UPC Number	785007108729	Country Of Origin	Mexico
Material	Nickel, Thermoplastic	Features	Durable
Installation Location	Underfloor	Application Sector	Commercial, Residential
Standard	Residential/Commercial	Warranty Type	1-Year Limited Warranty
Type	Floor Box		

Dimensions

Product Width US	3.25 in	Product Volume US	20.5 cu in
Product Depth US	4.0 in	Product Height US	4.75 in
Product Length US	4.75 in	Cubic Capacity	20.5 in ³

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Rectangular
Mounting Type	Screw Mount		
