



Pass and Seymour
Tamper-Resistant Floor Box Assembly - Two Gang for Wood Sub-Floors, Brass
Part No. FB2TRDR2B



Tamper-Resistant Floor Box Assembly, Two #8 duplex openings, Four threaded screw plugs. Includes two 3232 15A, 125A tamper-resistant duplex receptacles. Brass. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out. Rugged diecast cover plates with durable nickel or brass finish.
- Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors. Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.
- Large box flange rests on finished floor -- no adjustments needed. Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.
- Extra-deep design leaves plenty of wiring room.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007108705	Country Of Origin	Mexico
Material	Brass, Thermoplastic	Features	Durable
Installation Location	Underfloor	Application Sector	Commercial, Residential
Standard	Residential/Commercial	Warranty Type	1-Year Limited Warranty
Type	Floor Box		

Dimensions

Product Width US	6.5 in	Product Volume US	42.5 cu in
------------------	--------	-------------------	------------

Product Depth US	4.0 in	Product Height US	4.75 in
Product Length US	4.75 in	Cubic Capacity	42.5 in³

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	2	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Rectangular
Mounting Type	Screw Mount		