



Pass and Seymour
Flexcor® Support Grips Standard Duty, Closed Mesh, Single-Eye Grip, Cable Diameter 0.62 - 0.74 in.
Part No. FC062U



FC062U: Standard Duty, Closed Mesh, Single-Eye Grip, Cable Diameter 0.62 - 0.74 inches, Bale Length 8-in, Mesh Length 11-in, Break Strength 960 lbs.

Features & Benefits

Closed mesh support grips are used when the end of the cable is accessible.

Standard duty closed mesh support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 8: Mesh Length: 11

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007980677
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

Dimensions

Product Width US	0.74 in	Product Length US	10.0 in
Mesh Length	10 in	Cable Diameter Range	0.630-0.740 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Mesh Type	Closed	Approximate Break Strength	890 lb
Maximum Cable Range	0.62 in	Eye Style	Single
Minimum Cable Range	0.74 in	Capacity	Various Cable Diameter Ranges

Indoor/Outdoor	Both	Mounting	Consult the Factory for Mounting Recommendations
----------------	------	----------	--