



FS100U: Standard Duty, Split Lace, Single Eye, Cable Diameter 1.00 - 1.24 inches, Bale Length 9-in, Mesh Length 15-in, Break Strength 1680 lbs.

Features & Benefits

Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.

Split lace support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 9; Mesh Length: 15

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007984200
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

Dimensions

Mesh Length	13.5 in	Cable Diameter Range	1.00-1.24 in
-------------	---------	----------------------	--------------

Technical Information

Mesh Type	Split Lace	Approximate Break Strength	1610 lb
Maximum Cable Range	1 in	Eye Style	Single
Minimum Cable Range	1.24 in	Capacity	Various Cable Diameter Ranges
Indoor/Outdoor	Both	Mounting	Consult the Factory for Mounting Recommendations