



radiant Collection
radiant® Multi-Location Master Dimmer, White
Part No. HCL453PMMW



Allows precise dimming control of a light or fixture. Pair with a Multi-Location Remote Dimmer to control the same fixture from another spot in the room. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

For use with most incandescent, CFL/LED (with the exception of 0 - 10v options) and MLV dimmable bulbs. Installs easily with 3-way wiring for multi-location dimming (use with up to nine remote dimmers).

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Can also be used in single-pole applications for solitary control.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating* required in multi-gang applications.

*Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007039665
Country Of Origin	China	Material	Steel, Thermoplastic

Features	Color Change Kit, High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)		Switch Type	Digital, Paddle
Number of Switches	1		Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed		Warranty Type	Limited Lifetime Warranty
Type	Dimmer			
Dimensions				
Product Width US	2.5 in		Product Depth US	1.25 in
Product Height US	4.25 in			
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	E95219		cULus Listed	Yes
Technical Information				
Load Rating	120V 450W (CFL), 120V 450W (LED), 120V 700VA (MLV), 120V 700W (Halogen), 120V 700W (Incandescent)		Dimming Compatibility	Forward Phase
Frequency Rating	60 Hz		Maximum Humidity	95% (relative humidity, non-condensing)
Number of Poles	Multi-Location, Single Pole 3-Way		Wire Size	#14 - #10 AWG
Requires Neutral Wire	No		Indoor/Outdoor	Indoor
Mounting Type	Wall Box		Wire Connection Type	Screw Terminals
Voltage	120 VAC		Load Type	CFL, Incandescent, LED
Environmental Conditions	Humidity: Less than 95% non condensing			