



Pass and Seymour
Isolated Ground TVSS Quad Receptacle, Ivory
Part No. IG420HISP



Isolated Ground Hospital Grade TVSS Quad Receptacle, 20A 125V

Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007125740	Country Of Origin	Mexico
Number of Receptacles	4	Features	Brass Mounting Strap, Indicator Lights
Outlet Type	Isolated Ground, Locking	Application Sector	Commercial
Wall Plate Included	No	Standard	UL1449, UL498: ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).
Warranty Type	1-Year Limited Warranty		

Technical Information

Connection Location	Back and Side	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Mounting Type	Box
Wire Connection Type	Screw Terminals	Voltage	125/250 V
Environmental Conditions	Flammability: UL94 V2 and UL94-5 VA		