



Turnlok Registered Single Receptacle 3-Wire 15A 125V Isolated Ground

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Side and external screw-pressure-plate back wire capability. Accepts #14-#10 AWG.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007647105	Country Of Origin	Mexico
Number of Receptacles	1	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Isolated Ground, Locking	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.437 in	Product Depth US	1.0 in
------------------	----------	------------------	--------

Product Height US	2.25 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	16063

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	L5-15R
Wire Connection Type	Screw Terminals	Voltage	125.0 V