



Pass and Seymour
Turnlok® Isolated Ground Single Receptacle 15A 277V, Orange
Part No. IG4760



Turnlok Registered Single Receptacle 3-Wire 15A 277V Isolated Ground

Features & Benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability. Accepts #14-#10 AWG.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	UPC Number	785007647600
Country Of Origin	Mexico	Number of Receptacles	1
Features	Impact Resistant	Outlet Type	Locking
Application Sector	Industrial	Wall Plate Included	No
Standard	UL Listed	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.437 in	Product Depth US	4.03 in
Product Height US	1.203 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	16063

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	L7-15R
Wire Connection Type	Screw Terminals	Voltage	277.0 V