



Turnlok Registered Receptacle 3-Wire 20A 125/250V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007102055	Country Of Origin	Mexico
Number of Receptacles	1	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Locking	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
------------------	---------	------------------	---------

Product Height US	2.29 in
-------------------	---------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	3	Amperage	20 A
Number of Poles	3-Way	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	L10-20R
Wire Connection Type	Screw Terminals	Voltage	125/250 V