



Pass and Seymour  
20A NEMA Plug L1220 - Black Back, White Front Body  
Part No. L1220P



Turnlok Registered Plug 3-Wire 20A 3-Phase 480V

## Features & Benefits

|                                                                                             |                                                                                                                                                      |
|---------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.           | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.                                |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock.               | Double dovetail design provides superior protection against cord pull-out forces.                                                                    |
| Impact- and corrosion-resistant durable nylon 6 shell material.                             | Rounded back contour reduces snags and hang-ups on the job site.                                                                                     |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal.       | Visible stamped NEMA configuration and device rating.                                                                                                |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

## Specifications

### General Info

|              |                |                    |            |
|--------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color              | Black      |
| UPC Number   | 785007122046   | Country Of Origin  | Mexico     |
| Features     | Locking        | Application Sector | Commercial |
| Standard     | UL 498         | Warranty Type      | 1-Year     |
| Type         | Plug           |                    |            |

### Dimensions

|                  |        |                   |         |
|------------------|--------|-------------------|---------|
| Product Width US | 2.2 in | Product Length US | 2.57 in |
|------------------|--------|-------------------|---------|

---

Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

Technical Information

---

|                 |         |         |    |
|-----------------|---------|---------|----|
| Connector Style | Locking | Flanged | No |
|-----------------|---------|---------|----|

---

|                        |                   |                 |   |
|------------------------|-------------------|-----------------|---|
| Terminal Accommodation | #18 AWG - #10 AWG | Number of Wires | 3 |
|------------------------|-------------------|-----------------|---|

---

|          |      |                 |       |
|----------|------|-----------------|-------|
| Amperage | 20 A | Number of Poles | 3-Way |
|----------|------|-----------------|-------|

---

|                |        |                         |         |
|----------------|--------|-------------------------|---------|
| Indoor/Outdoor | Indoor | NEMA Configuration Code | L12-20P |
|----------------|--------|-------------------------|---------|

---

|                  |   |         |         |
|------------------|---|---------|---------|
| Number of Phases | 3 | Voltage | 480.0 V |
|------------------|---|---------|---------|

---