



Pass and Seymour  
20A NEMA Plug L1420 - Black Back, White Front Body  
Part No. L1420P

Turnlok Registered Plug 4-Wire 20A 125/250V



### Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6 shell material.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

New-design external cord grips provide visible assurance of safe and proper cord retention.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Double dovetail design provides superior protection against cord pull-out forces.

Rounded back contour reduces snags and hang-ups on the job site.

Visible stamped NEMA configuration and device rating.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

### Specifications

|              |                 |                    |            |
|--------------|-----------------|--------------------|------------|
| General Info |                 |                    |            |
| Product Line | Pass & Seymour  | Color              | Black      |
| UPC Number   | 785007142044    | Country Of Origin  | Mexico     |
| Features     | Locking         | Application Sector | Industrial |
| Standard     | UL 498, FEDSPEC | Warranty Type      | 1-Year     |
| Type         | Plug            |                    |            |

### Dimensions

|                  |        |                   |         |
|------------------|--------|-------------------|---------|
| Product Width US | 2.2 in | Product Length US | 2.57 in |
|------------------|--------|-------------------|---------|

**Listing Agencies / 3rd Party Agencies**

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

**Additional Information**

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

**Technical Information**

|                        |           |                         |             |
|------------------------|-----------|-------------------------|-------------|
| Connector Style        | Locking   | Flanged                 | No          |
| Terminal Accommodation | #4 AWG    | Number of Wires         | 3           |
| Amperage               | 20 A      | Number of Poles         | Double Pole |
| Indoor/Outdoor         | Indoor    | NEMA Configuration Code | L14-20P     |
| Voltage                | 125/250 V |                         |             |