



Turnlok Registered Single Receptacle 4-Wire 20A 3-Phase 250V



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.	.032 inch thick, brass, triple-wipe power contacts for lasting retention.
One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.	Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.	Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007152050
Country Of Origin	Mexico	Number of Receptacles	1
Features	Brass Mounting Strap, Impact Resistant	Outlet Type	Locking
Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 498, Fedspec	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
------------------	---------	------------------	---------

Product Height US	2.29 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection Location	Back and Side	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	L15-20R	Wire Connection Type	Screw Terminals
Voltage	250.0 V		