



Pass and Seymour
30A NEMA L1830 Plug - Black Back, White Front Body
Part No. L1830P

Plug 4-Wire 30A 120/208Volt Turnlok Registered



Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible assurance of safe and proper cord retention.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007183047	Country Of Origin	Mexico
Features	Locking	Application Sector	Industrial
Standard	UL 498	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	2.2 in	Product Length US	2.57 in
------------------	--------	-------------------	---------

Additional Information

Product Environmental Profile Yes

Technical Information

Connector Style	Locking	Flanged	No
Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way
Indoor/Outdoor	Indoor	NEMA Configuration Code	L18-30P
Number of Phases	3	Voltage	125/208 V