



Pass and Seymour
30A NEMA L1930 Connector - Black Back, White Front Body
Part No. L1930C

Connector 4-Wire 30A 277/480V Turnlok Registered



Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007193015	Country Of Origin	Mexico
Features	Corrosion Resistant	Application Sector	Commercial
Standard	UL 498	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Width US	2.2 in	Product Length US	3.33 in
------------------	--------	-------------------	---------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connector Style	Locking	Flanged	No
-----------------	---------	---------	----

Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	4
------------------------	-------------------	-----------------	---

Amperage	30 A	Number of Poles	4-Way
----------	------	-----------------	-------

Indoor/Outdoor	Indoor	NEMA Configuration Code	L19-30R
----------------	--------	-------------------------	---------

Number of Phases	3	Voltage	277/480 VAC
------------------	---	---------	-------------
