



Pass and Seymour
20A 277/480V NEMA L2220 Single Receptacle, 5-Wire, Black
Part No. L2220R

Receptacle Single 5-Wire 20A 277/480V Turnlok Registered



Features & Benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Side and external screw-pressure-plate back wire capability.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007222050
Country Of Origin	Mexico	Number of Receptacles	1
Features	Brass Mounting Strap, Impact Resistant	Outlet Type	Locking
Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
------------------	---------	------------------	---------

Product Height US	2.29 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection Location	Back and Side	Number of Wires	5
Amperage	20 A	Number of Poles	4 Pole
Wire Size	18 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	L22-20R	Wire Connection Type	Screw Terminals
Voltage	277/480 VAC		