



Pass and Seymour
20A 125V NEMA L520 Single Receptacle, 2-Pole 3-Wire, Black
Part No. L520R



Turnlok Registered Receptacle Single, 2-Pole 3-Wire, 20A 125V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007252057
Country Of Origin	Mexico	Number of Receptacles	1
Features	Brass Mounting Strap	Outlet Type	Locking
Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Temperature Min	-40 °C	Connection Location	Back and Side
---------------------------	--------	---------------------	---------------

Operating Temperature Max	75 °C	Amperage	20 A
---------------------------	-------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	L5-20R
----------------	--------	-------------------------	--------

Operating Temperature	-40°-75°C	Wire Connection Type	Internal Pressure Plates, Screw Terminals
-----------------------	-----------	----------------------	--

Voltage	125.0 V
---------	---------