



Pass and Seymour
20A 250V NEMA L620 Single Receptacle, 3-Wire, Black
Part No. L620R



Turnlok Registered Receptacle Single 3-Wire 20A 250V

Features & Benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Side and external screw-pressure-plate back wire capability.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007262056
Country Of Origin	Mexico	Number of Receptacles	1
Features	Brass Mounting Strap, Indicator Lights	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Temperature Min	-40 °C	Connection Location	Back and Side
---------------------------	--------	---------------------	---------------

Number of Wires	3	Operating Temperature Max	75 °C
-----------------	---	---------------------------	-------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

NEMA Configuration Code	L6-20R	Operating Temperature	-40°-75°C
-------------------------	--------	-----------------------	-----------

Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	250.0 V
----------------------	---	---------	---------