



Pass and Seymour
30A NEMA L630 Connector - Black Back, White Front Body
Part No. L630C

Turnlok Registered Connector 3-Wire 30A 250V



Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6 shell material.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

New-design external cord grips provide visible assurance of safe and proper cord retention.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Double dovetail design provides superior protection against cord pull-out forces.

Rounded back contour reduces snags and hang-ups on the job site.

Visible stamped NEMA configuration and device rating.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007263015	Country Of Origin	Mexico
Features	Corrosion Resistant	Application Sector	Industrial
Standard	UL 498, FEDSPEC	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Width US	2.2 in	Product Length US	3.33 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Connector Style	Locking	Flanged	No
Terminal Accommodation	#4 AWG	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	L6-30R
Voltage	250.0 V		