



Pass and Seymour  
LS Series CFL/LED/Incandescent 3-Way Slide Dimmer, Non-Preset, White  
Part No. LSCL453PW



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)

Single pole/3-way versions

Unique integrated single pole/3-way dimmer control

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

## Specifications

### General Info

|                    |                           |                    |                          |
|--------------------|---------------------------|--------------------|--------------------------|
| Product Line       | Pass & Seymour            | Color              | White                    |
| Finish             | Matte                     | UPC Number         | 785007040395             |
| Country Of Origin  | China                     | Material           | Steel, Thermoplastic     |
| Product Series     | Trademaster               | Features           | Low-End Trim (Dim Range) |
| Switch Type        | Rocker, Slider            | Number of Switches | 1                        |
| Application Sector | Residential               | Standard           | cULus, RoHS              |
| Warranty Type      | Limited Lifetime Warranty | Type               | Dimmer                   |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.74 in | Product Depth US | 1.28 in |
| Product Height US | 4.19 in |                  |         |

Technical Information

|                       |                                         |                          |                                                                                           |
|-----------------------|-----------------------------------------|--------------------------|-------------------------------------------------------------------------------------------|
| Preset                | Yes                                     | Load Rating              | 120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent) |
| Dimming Compatibility | Forward Phase                           | Frequency Rating         | 60 Hz                                                                                     |
| Maximum Humidity      | 95% (relative humidity, non-condensing) | Number of Poles          | Single Pole 3-Way                                                                         |
| Wire Size             | #14 - #10 AWG                           | Requires Neutral Wire    | No                                                                                        |
| Indoor/Outdoor        | Indoor                                  | Mounting Type            | Wall Box                                                                                  |
| Wire Connection Type  | Screw Terminals                         | Voltage                  | 120 VAC                                                                                   |
| Load Type             | CFL, Halogen, Incandescent, LED         | Environmental Conditions | Humidity: Less than 95% non condensing                                                    |