



Pass and Seymour
LS Series Dual Fan Speed Control Dimmer, White
Part No. LSDC163PWV



Dual Control Slides

Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007238877
Country Of Origin	China	Material	Steel, Thermoplastic
Product Series	Trademaster	Features	Combination, De-Hummer Fan Control, Low-End Trim (Dim Range)
Switch Type	Rocker, Slider	Number of Switches	2
Application Sector	Residential	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.185 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Preset	Yes	Load Rating	120V 1.6A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)
Operating Cycles	100000	Dimming Compatibility	Forward Phase
Frequency Rating	60 Hz	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Flying Leads	Voltage	120 VAC
Load Type	Fan Motor, Incandescent		