



Pass and Seymour
LS Series Fan Speed Control/Dimmer, Ivory
Part No. LSDC16IV



Dual Slide 3-Speed De-Hummer Fan Control with Single-Pole Dimmer

Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Device comes with wired leads.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Gloss	UPC Number	785007236064
Country Of Origin	China	Material	Steel, Thermoplastic
Product Series	Trademaster	Features	Combination, De-Hummer Fan Control, Low-End Trim (Dim Range)
Switch Type	Slider	Number of Switches	2
Application Sector	Residential	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	109655	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Load Rating	120V 1.6A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)	Operating Cycles	100000
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120 VAC	Load Type	Fan Motor, Incandescent