



Pass and Seymour  
LS Series Fan Speed Control, White  
Part No. LSDH16WV



Decorator Slide De-Hummer Control, 4-Speed, 1.6A

## Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Device comes with wired leads.

Can be used with patented Snap-In Light Module (sold separately).

## Specifications

### General Info

|                    |                                                              |                    |                                  |
|--------------------|--------------------------------------------------------------|--------------------|----------------------------------|
| Product Line       | Pass & Seymour                                               | Color              | White                            |
| Finish             | Matte                                                        | UPC Number         | 785007157864                     |
| Country Of Origin  | China                                                        | Material           | Steel, Thermoplastic             |
| Features           | 4-Speed Fan Control, Color Change Kit, De-Hummer Fan Control | Switch Type        | Slider                           |
| Number of Switches | 1                                                            | Application Sector | Multi-Dwelling Unit, Residential |
| Standard           | UL Listed                                                    | Warranty Type      | Limited Lifetime Warranty        |
| Type               | Fan Speed Control                                            |                    |                                  |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.74 in | Product Depth US | 1.28 in |
|------------------|---------|------------------|---------|

|                   |          |
|-------------------|----------|
| Product Height US | 4.185 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|        |    |             |                       |
|--------|----|-------------|-----------------------|
| Preset | No | Load Rating | 120V 1.6A (FAN MOTOR) |
|--------|----|-------------|-----------------------|

|                  |        |                       |                |
|------------------|--------|-----------------------|----------------|
| Operating Cycles | 100000 | Dimming Compatibility | Fan Speed Only |
|------------------|--------|-----------------------|----------------|

|                  |       |                 |             |
|------------------|-------|-----------------|-------------|
| Frequency Rating | 60 Hz | Number of Poles | Single Pole |
|------------------|-------|-----------------|-------------|

|           |               |                       |    |
|-----------|---------------|-----------------------|----|
| Wire Size | #14 - #10 AWG | Requires Neutral Wire | No |
|-----------|---------------|-----------------------|----|

|                |        |               |          |
|----------------|--------|---------------|----------|
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
|----------------|--------|---------------|----------|

|                      |              |         |         |
|----------------------|--------------|---------|---------|
| Wire Connection Type | Flying Leads | Voltage | 120 VAC |
|----------------------|--------------|---------|---------|

|           |              |
|-----------|--------------|
| Load Type | AC Fan Motor |
|-----------|--------------|