



Pass and Seymour
LS Series Fan Speed Control, Black
Part No. LSSC5BK

Decorator Slide Fan Control, Preset/3-Speed/5A



Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007045550
Country Of Origin	China	Material	Steel, Thermoplastic
Features	Variable Speed Fan Control	Switch Type	Slider
Number of Switches	1	Application Sector	Multi-Dwelling Unit, Residential
Standard	UL/CSA Listed	Warranty Type	Limited Lifetime Warranty
Type	Fan Speed Control		

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
------------------	---------	------------------	---------

Product Height US	4.185 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Preset	No	Load Rating	120V 5A (Fan Control)
--------	----	-------------	-----------------------

Operating Cycles	100000	Dimming Compatibility	Fan Speed Only
------------------	--------	-----------------------	----------------

Frequency Rating	60 Hz	Number of Poles	Single Pole
------------------	-------	-----------------	-------------

Wire Size	#14 - #12 AWG	Requires Neutral Wire	No
-----------	---------------	-----------------------	----

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

Wire Connection Type	Screw Terminals	Voltage	120 VAC
----------------------	-----------------	---------	---------

Load Type	AC Fan Motor
-----------	--------------