



Pass and Seymour
Old Work Metal Switch and Outlet Box
Part No. M118W



Single gang metal box. Swing bracket for mounting adjusts 1 1/4" down to 1/4". Four 3/4" x 1 1/4" KOs plus integral Romex clamp.

Features & Benefits

Large 18 cubic inch box volume	Handles conduit, armored cable or romex
4 Concentric Knock-outs 1/2" or 3/4"	Romex cable entry with integral cable clamp
Simple rectangular cut-out	Swing bracket mounting in existing wall surfaces
No intrusive hardware	Fits in standard 2 x 4 stud cavity

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007030167	Country Of Origin	China
Material	Steel	Features	Integral Clamp, Old Work, Shallow
Number of Knockouts	4	Application Sector	Commercial, Residential
Standard	cULus, UL Listed, RoHS	Warranty Type	1-Year Limited Warranty
Type	Switch & Outlet Boxes		

Dimensions

Product Width US	2.25 in	Product Weight US	16.5 lb
Product Volume US	18.0 cu in	Product Depth US	3.0 in

Product Height US	3.25 in	Product Length US	3.25 in
Cubic Capacity	18 in³		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Rectangular
Mounting Type	Swing Bracket		