



Pass and Seymour
Switch and Outlet Box
Part No. P354RACMH



Triple Gang, Switch and Outlet Box with captive Mounting Nails on Each End, Six Auto/Clamps on Each End, 3 1/16-inch depth for manufactu housing walls. 50 pack.

Features & Benefits

Durable, impact-resistant thermoplastic box.

Easy Installation, rectangular cutout

Innovative extras that cut installation time.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007269987	Country Of Origin	United States
Material	Thermoplastic	Features	Auto Clamps, Quick Entry
Installation Location	Wall	Number of Knockouts	12
Application Sector	Commercial, Residential	Standard	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Outlet Box

Dimensions

Product Width US	5.938 in	Product Weight US	0.4 lb
Product Volume US	54.0 cu in	Product Depth US	3.063 in
Product Height US	3.813 in	Product Length US	3.813 in
Cubic Capacity	54 in ³		

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Gangs	3	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Rectangular
Mounting Type	Nail On		
