



4-Way Toggle Switch, Back and Side-Wire, 15A 120/277V

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007196757
Country Of Origin	Mexico	Material	Thermoplastic
Features	Chemical Resistant	Switch Type	Toggle

Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 20, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Switch
Dimensions			
Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus ListingNumber	140597
cULus Listed	Yes		
Technical Information			
Load Rating	15 A @ 120/277 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Double Throw	Amperage	15 A
Number of Poles	4-Way	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC, 277 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		