



Pass and Seymour
30A 120/277VAC B+S WIRE DP SW BROWN, HP RATED
Part No. PS30AC2HP



Double-Pole, Single Phase Switch, Back and Side-Wire, HP Rated.
30A, 277V.

Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life.

Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

Made in USA. Box lug terminals. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007195972
Country Of Origin	Mexico	Material	Thermoplastic
Features	Chemical Resistant	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 20, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Load Rating	30 A @ 120/277 VAC	Connection Location	Back and Side
Horsepower Rating	2 HP @ 120 VAC, 2 HP @ 240 VAC	Terminal Accommodation	#14 AWG - #10 AWG
Number of Gangs	1	Throw Type	Double Throw
Amperage	30 A	Number of Poles	Double Pole
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120.0 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon