



2-Pole Pilot Lighted Switch, Back and Side-Wire, 30A 120/277V

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	UPC Number	785007195941
Country Of Origin	Mexico	Material	Thermoplastic
Features	Chemical Resistant	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 20, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Load Rating	30 A @ 120/277 VAC	Connection Location	Back and Side
-------------	--------------------	---------------------	---------------

Horsepower Rating	2 HP @ 120 VAC, 2 HP @ 240 VAC	Terminal Accommodation	#14 AWG - #10 AWG
-------------------	--------------------------------	------------------------	-------------------

Number of Gangs	1	Throw Type	Double Throw
-----------------	---	------------	--------------

Amperage	30 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Requires Neutral Wire	No	Indoor/Outdoor	Indoor
-----------------------	----	----------------	--------

Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
---------------	----------	----------------------	-----------------

Voltage	120/277 V	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
---------	-----------	-----------	--
