



Pass and Seymour
100A 2 Pole 3 Wire Non-Fusible Mechanical Interlock
Part No. PS3100MIR6W



Double pole, Triple wire, Non-Fusible Mechanical Interlock. 100 amp, 240 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007015614	Country Of Origin	United States
Features	Corrosion Resistant, Durable, Watertight	Application Sector	Industrial
Standard	UL Listed	Warranty Type	1-Year
Type	Interlock		

Dimensions

Product Width US	6.88 in	Product Depth US	9.5 in
Product Height US	14.13 in		

Technical Information

Flanged	No	Number of Wires	3
Amperage	100 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Number of Phases	3
Voltage	250.0 V		