



Pass and Seymour
Series 16 In-Line Connectors
Part No. PS40FBW



400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow

Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance	Exceptional seal for maintaining NEMA Type 3R and 4 integrity
Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product	Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
Heavy-duty hex set screws allow greater termination torque	Copper wire provides quality strain relief
Copper shim bundles wire strands to reduce "splaying."	

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007308167	Country Of Origin	Mexico
Features	Chemical Resistant	Application Sector	Commercial, Industrial
Standard	UL, cCSAus	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Length US	6.8 in
-------------------	--------

Technical Information

Operating Temperature Min	-40 °C	Flanged	No
Terminal Accommodation	2/0 - 4/0	Operating Temperature Max	75 °C
Amperage	400 A	Number of Poles	Single Pole
Indoor/Outdoor	Indoor	Operating Temperature	-40°-75°C
Voltage	600.0 V	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4