

400A 600V FEMALE CAM DSS PNL MT



Features & Benefits

Nylon housing provides outstanding impact and chemical resistance. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity.

Heavy-duty hex set screws (available on double set screw version only) allow greater termination torque.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007308365	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL, cUL

Dimensions

Product Width US	2.25 in	Product Weight US	0.75 lb
Product Volume US	21.516 cu in	Product Depth US	4.25 in
Product Height US	2.25 in		

Technical Information

Operating Temperature Min	-40 °C	Connection	Double Set Screw
Operating Temperature Max	75 °C	Amperage	400 A
Wire Size	2/0 - 4/0	Operating Temperature	-40°-75°C

Voltage	600.0 V	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
---------	---------	--------------------------	---
