



Pass and Seymour
Pin & Sleeve Watertight 100A 3ØY 120V/208V Plug
Part No. PS5100P9W



4-Pole, 5-Wire, Pin and Sleeve Plug. 100A, 3Y, 120/208 vac.

Features & Benefits

Legrand Pin & Sleeve products provide installation ease, enduring performance in harsh conditions, and guaranteed IEC 309 compatibility.

Nylon construction for high impact and corrosion resistance.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.

Combination-head screws for added convenience and quick installation.

Cover with integral neoprene gasket provides watertight seal.

Arrives ready to wire, with cord grip open and cable-ready. Terminal screws come backed out and ready to wire. Front and back body require no disassembly prior to assembly.

Nickel-plated brass pins provide extra corrosion resistance without sacrificing electrical conductivity.

Natural-rubber grommets provide watertight protection at cable entry.

Revolutionary, hinged cord grip for durable performance and ease of installation.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007051018	Country Of Origin	United States
Features	Watertight	Application Sector	Commercial
Standard	UL Listed	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	5.2 in	Product Height US	5.2 in
Product Length US	13.4 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	151347	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connector Style	Pin & Sleeve	Flanged	No
Terminal Accommodation	#2 AWG	Number of Wires	5
Amperage	100 A	Number of Poles	4-Way
Indoor/Outdoor	Both	Voltage	120.0 V