



Straight Blade Plug 2-Pole 3-Wire 15A 125V Gray

## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance.

Rugged two-piece cord grip provides more uniform cord retention.

Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|              |                                             |                    |            |
|--------------|---------------------------------------------|--------------------|------------|
| Product Line | Pass & Seymour                              | Color              | Black      |
| UPC Number   | 785007236903                                | Country Of Origin  | Mexico     |
| Features     | Chemical Resistant, Durable, Dust Resistant | Application Sector | Industrial |
| Standard     | UL 498                                      | Warranty Type      | 1-Year     |
| Type         | Plug                                        |                    |            |

### Dimensions

|                  |          |                   |          |
|------------------|----------|-------------------|----------|
| Product Width US | 1.516 in | Product Length US | 1.752 in |
|------------------|----------|-------------------|----------|

---

Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

|                         |                |                |                |
|-------------------------|----------------|----------------|----------------|
| Connector Style         | Straight Blade | Flanged        | No             |
| Terminal Accommodation  | #4 AWG         | Connection     | Wire Grounding |
| Number of Wires         | 3              | Amperage       | 15 A           |
| Number of Poles         | Double Pole    | Indoor/Outdoor | Indoor         |
| NEMA Configuration Code | 5-15P          | Voltage        | 125.0 V        |

---