

Straight Blade Plug 2-Pole 3-Wire 20A 125A



Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007237573	Country Of Origin	Mexico
Features	Durable	Application Sector	Commercial
Standard	UL 498, FEDSPEC	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
------------------	---------	------------------	---------

Product Height US	1.83 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E146159	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Connector Style	Straight Blade	Flanged	No
Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20P
Voltage	125.0 V		