



Pass and Seymour  
Straight Blade CONN 3W 15A 250V HG PS5669XHG  
Part No. PS5669XHG

Straight Blade Connector 2-Pole 3-Wire 15A 250V Hospital Grade



## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Rugged two-piece cord grip provides more uniform cord retention.

Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Nylon housing provides impact and chemical resistance.

Internal dust shield keeps terminals free of contaminants.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

## Specifications

### General Info

|              |                                             |                    |                                     |
|--------------|---------------------------------------------|--------------------|-------------------------------------|
| Product Line | Pass & Seymour                              | Color              | Black                               |
| UPC Number   | 785007236866                                | Country Of Origin  | Mexico                              |
| Features     | Chemical Resistant, Durable, Dust Resistant | Application Sector | Commercial, Healthcare, Residential |
| Standard     | UL498, FEDSPEC                              | Warranty Type      | 1-Year                              |
| Type         | Connector                                   |                    |                                     |

### Dimensions

|                  |          |                   |          |
|------------------|----------|-------------------|----------|
| Product Width US | 1.358 in | Product Length US | 2.638 in |
|------------------|----------|-------------------|----------|

Listing Agencies / 3rd Party Agencies

cULus Listed                      Yes

Additional Information

Product Environmental Profile    Yes

Technical Information

|                        |                   |                         |             |
|------------------------|-------------------|-------------------------|-------------|
| Connector Style        | Straight Blade    | Flanged                 | No          |
| Terminal Accommodation | #18 AWG - #12 AWG | Number of Wires         | 3           |
| Amperage               | 15 A              | Number of Poles         | Double Pole |
| Indoor/Outdoor         | Indoor            | NEMA Configuration Code | 6-15P       |
| Number of Phases       | 3                 | Voltage                 | 250.0 V     |