



Pass and Seymour
MaxGrip M3 Plug, Orange
Part No. PS5965O



STR BLD PLUG 3W 15A125A

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Enclosed terminals provide solid, internally-clamped connections.

High-visibility yellow and orange, or gray.

For covering patents, see www.legrand.us/patents.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Molded finger grips promote safe, sure handling.

Hospital Grade version displays the Hospital Grade green dot.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007237498	Country Of Origin	Mexico
Features	Durable	Application Sector	Commercial
Standard	UL Listed	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Height US	1.83 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E146159	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Connector Style	Straight Blade	Flanged	No
-----------------	----------------	---------	----

Terminal Accommodation	#18 AWG - #12 AWG	Number of Wires	3
------------------------	-------------------	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15P
----------------	--------	-------------------------	-------

Voltage	125.0 V		
---------	---------	--	--