



Pass and Seymour
MaxGrip M3 Connector, Orange
Part No. PS59690



STRAIGHT BLADE CONNECTOR, 3-Wire 15A-125A

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007237542	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL498

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Height US	1.83 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E146159	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Phase	Three	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 - 12 AWG		
