



Pass and Seymour
MaxGrip M3 Connector, Yellow
Part No. PS5969Y



Straight Blade Connector 2-Pole 3-Wire 15A 125A

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007237511	Country Of Origin	Mexico
Features	Gripping Connectors	Application Sector	Commercial, Residential
Standard	UL 498	Warranty Type	1-Year
Type	Connector		

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
------------------	---------	------------------	---------

Product Length US	1.83 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E146159	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Connector Style	Straight Blade	Flanged	No
-----------------	----------------	---------	----

Terminal Accommodation	#4 AWG	Connection	Wire Grounding
------------------------	--------	------------	----------------

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

NEMA Configuration Code	5-15R	Voltage	125.0 V
-------------------------	-------	---------	---------