



Decorator Combo Switch

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007305913
Country Of Origin	China	Material	Thermoplastic
Features	Chemical Resistant, Combination, Decorator Style	Switch Type	Paddle
Number of Switches	2	Application Sector	Commercial, Industrial

Wall Plate Included	No	Standard	cULus UL20
Warranty Type	1-Year Limited Warranty	Type	Combination Switch
Dimensions			
Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.812 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Load Rating	20 A @ 277 VAC	Contact Configuration	N-0
Operating Cycles	50000	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Double Throw	Amperage	20 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	277 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Environmental Conditions	Flammability: UL94 V2