



Pass and Seymour
PlugTail® Single Pole 15A Decorator Switch, White
Part No. PT2601W



PlugTail Registered Single-Pole 15A Decorator Switch

Features & Benefits

Ground wire pre-mounted to the box

4" square x 1 1/2" or 2 1/8" metal boxes

All Double Gang Kits contain two right angle PlugTail connectors

Mud ring factory installed

PlugTail Right Angle Connectors with 12 AWG copper pigtails

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007001037
Country Of Origin	Mexico	Material	Thermoplastic
Features	Decorator Style	Number of Switches	1
Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 20	Warranty Type	1-Year Limited Warranty
Type	Decorator, Switch		

Dimensions

Product Width US	1.3 in	Product Depth US	1.06 in
------------------	--------	------------------	---------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
---------------------	-----------	------------------------	-------------------

Number of Gangs	1	Throw Type	Single Throw
-----------------	---	------------	--------------

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Requires Neutral Wire	No	Indoor/Outdoor	Indoor
-----------------------	----	----------------	--------

Mounting Type	Wall Box	Wire Connection Type	PlugTail
---------------	----------	----------------------	----------

Voltage	120/277 V
---------	-----------